

Special Stems for Gas-actuated Thermometers

A2 / A7

A7.1

Stem without bent tube

Connection screw fitting adjustable at the capillary line

Application

For difficult installation conditions and overlong thermowells.

Standard Versions

For thermometers, with capillary line ① between thermometer and vessel ② (active length L_a), connection screw fitting ③ turnable and adjustable at the capillary line, capillary line wetted, if applicable.

Temperature Sensor (Vessel)

Made of stainless steel 1.4571 (316Ti)
Stem models optionally: A2, A7 or A7.1

Stem \varnothing dF

8, 10 or 12 mm

Capillary Line

Stainless steel, \varnothing 2 mm


Buckle protection to thermometer case

Capillary Line Length

$L_{FL} = 1$ m to 15 m

Material Connection Screw Fitting

Stainless steel 1.4571 (316Ti)



Options

- Other connection threads upon request
- Other stem (vessel) diameters upon request
- Capillary line > 15 m upon request

Stem Model:	A2	A7	A7.1																																																																																										
Process connection:	Union nut lateral retaining screw	Male thread, turnable/double male adapter lateral retaining screw	Male thread, clamping connection at capillary line																																																																																										
Specifics:	not sealing if applied without thermowell, only for unpressurised media	not sealing if applied without thermowell, only for unpressurised media	clamping ring FPM (Viton®) medium temperature: max. 180 °C																																																																																										
Order length:	L_{FL}	L_{FL}	L_{FL}																																																																																										
P max.:	unpressurised	unpressurised	1.5 bar																																																																																										
Suitable thermowell models: (data sheet)	SF4.1 (8.8111) SF4.1F (8.8113) SF8 (8.8130) SF9 (8.8131)	SF4 (8.8110) SF4F (8.8112) SF5 (8.8120) SF6, SF7 (8.8121)	SF4 (8.8110) SF4F (8.8112) SF5 (8.8120) SF6, SF7 (8.8121)																																																																																										
Thread (dimensional data in mm):	<table border="1"> <thead> <tr> <th>G</th> <th>SW</th> <th>i</th> </tr> </thead> <tbody> <tr> <td>G 1/2</td> <td>27</td> <td>10</td> </tr> <tr> <td>G 3/4</td> <td>32</td> <td>12</td> </tr> <tr> <td>M20x1.5</td> <td>27</td> <td>10</td> </tr> <tr> <td>M24x1.5</td> <td>32</td> <td>12</td> </tr> <tr> <td>M27x2</td> <td>32</td> <td>12</td> </tr> </tbody> </table>	G	SW	i	G 1/2	27	10	G 3/4	32	12	M20x1.5	27	10	M24x1.5	32	12	M27x2	32	12	<table border="1"> <thead> <tr> <th>G1</th> <th>G2</th> <th>SW1</th> <th>SW2</th> <th>i</th> </tr> </thead> <tbody> <tr> <td>G 1/2 B</td> <td>G 1/2 B</td> <td>27</td> <td>27</td> <td>14</td> </tr> <tr> <td>G 3/4 B</td> <td>G 1/2 B</td> <td>32</td> <td>27</td> <td>16</td> </tr> <tr> <td>1/2" NPT</td> <td>G 1/2 B</td> <td>27</td> <td>27</td> <td>19</td> </tr> <tr> <td>3/4" NPT</td> <td>G 1/2 B</td> <td>27</td> <td>27</td> <td>19</td> </tr> <tr> <td>M20x1.5</td> <td>M20x1.5</td> <td>27</td> <td>27</td> <td>14</td> </tr> <tr> <td>M24x1.5</td> <td>M20x1.5</td> <td>32</td> <td>27</td> <td>14</td> </tr> <tr> <td>M27x2</td> <td>M20x1.5</td> <td>32</td> <td>27</td> <td>16</td> </tr> </tbody> </table>	G1	G2	SW1	SW2	i	G 1/2 B	G 1/2 B	27	27	14	G 3/4 B	G 1/2 B	32	27	16	1/2" NPT	G 1/2 B	27	27	19	3/4" NPT	G 1/2 B	27	27	19	M20x1.5	M20x1.5	27	27	14	M24x1.5	M20x1.5	32	27	14	M27x2	M20x1.5	32	27	16	<table border="1"> <thead> <tr> <th>G</th> <th>SW1</th> <th>SW2</th> <th>i</th> </tr> </thead> <tbody> <tr> <td>G 1/2 B</td> <td>27</td> <td>17</td> <td>14</td> </tr> <tr> <td>G 3/4 B</td> <td>32</td> <td>17</td> <td>16</td> </tr> <tr> <td>1/2" NPT</td> <td>27</td> <td>17</td> <td>19</td> </tr> <tr> <td>3/4" NPT</td> <td>27</td> <td>17</td> <td>19</td> </tr> <tr> <td>M20x1.5</td> <td>27</td> <td>17</td> <td>14</td> </tr> <tr> <td>M24x1.5</td> <td>32</td> <td>17</td> <td>14</td> </tr> <tr> <td>M27x2</td> <td>32</td> <td>17</td> <td>16</td> </tr> </tbody> </table>	G	SW1	SW2	i	G 1/2 B	27	17	14	G 3/4 B	32	17	16	1/2" NPT	27	17	19	3/4" NPT	27	17	19	M20x1.5	27	17	14	M24x1.5	32	17	14	M27x2	32	17	16
G	SW	i																																																																																											
G 1/2	27	10																																																																																											
G 3/4	32	12																																																																																											
M20x1.5	27	10																																																																																											
M24x1.5	32	12																																																																																											
M27x2	32	12																																																																																											
G1	G2	SW1	SW2	i																																																																																									
G 1/2 B	G 1/2 B	27	27	14																																																																																									
G 3/4 B	G 1/2 B	32	27	16																																																																																									
1/2" NPT	G 1/2 B	27	27	19																																																																																									
3/4" NPT	G 1/2 B	27	27	19																																																																																									
M20x1.5	M20x1.5	27	27	14																																																																																									
M24x1.5	M20x1.5	32	27	14																																																																																									
M27x2	M20x1.5	32	27	16																																																																																									
G	SW1	SW2	i																																																																																										
G 1/2 B	27	17	14																																																																																										
G 3/4 B	32	17	16																																																																																										
1/2" NPT	27	17	19																																																																																										
3/4" NPT	27	17	19																																																																																										
M20x1.5	27	17	14																																																																																										
M24x1.5	32	17	14																																																																																										
M27x2	32	17	16																																																																																										

Thermowell recommended!

Thermowell recommended!

Active Length (mm)

Stem model:	Length:	Thread:	Capillary line including vessel < 5 m						Capillary line including vessel > 5 m to 15 m					
			up to max. 500 °C			500 °C and above			up to max. 500 °C			500 °C and above		
			Stem \varnothing dF:			Stem \varnothing dF:			Stem \varnothing dF:			Stem \varnothing dF:		
A2 / A7 / A7.1	L_a	all standard threads	12	10	8	12	10	8	12	10	8	12	10	8
			35	45	75	75	105	165	53	80	115	150	200	320

The active length L_a is the temperature-sensitive part of the stem.



Sales and Export South, West, North

ARMATURENBAU GmbH

Manometerstraße 5 • D – 46487 Wesel-Ginderich
Tel.: +49 2803 9130 – 0 • Fax: +49 2803 1035
www.armaturenbau.com • mail@armaturenbau.com

Subsidiary Company, Sales and Export East

MANOTHERM Beierfeld GmbH

Am Gewerbepark 9 • D – 08344 Grünhain-Beierfeld
Tel.: +49 3774 58 – 0 • Fax: +49 3774 58 – 545
www.manotherm.com • mail@manotherm.com

8299.2

03/17